Eaton 12105-12CHC

Catalog Number: 12105-12CHC

Eaton B-Line series JIC panel enclosure, 12" height, 5" length, 10" width, NEMA 12, Hinged cover, 12CHC enclosure Small single door, External mounting feet, Carbon steel, Seamless poured inplace gasket

General specifications

9.6 lb



UPC Product Length/Depth

782051750706 5 in

Product Height Product Width

12 in 10 in

Product Weight Certifications

CSA C22.2.

NEMA

UL 508A





Material/finish

Material

Carbon steel

Wall thickness

16 gauge

Finish color

Painted

Color

ANSI 61 gray

Model

Style

Small single door

Model

12CHC enclosure

Cover type

Hinged

Mounting method

Wall

Mounting hole details

External mounting feet

Closure type

Hinged

Special features

Cont. piano hinge, panel mount, plated door clamps

Standards

NEMA Rating

12

Country of origin

US

Resources

Catalogs

Electrical Enclosure Catalog

Specifications and datasheets

Eaton Specification Sheet - 12105-12CHC



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia