


1212120-GSC1-NK




	Catalog Number	1212120-GSC1-NK
	Marketing Product Description	12x120x12 Screw Cover Wireway Type 1 UL Listed Steel No Knockouts ANSI 61 Gray
	UPC	784572247062
	Length (IN)	120
	Width (IN)	12
	Height (IN)	12
	Weight (LB)	104
	Brand Name	Milbank
	Туре	Lay In Wireway
	Application	Wireway
	Standard	UL Listed
	Cover Type	Screw Cover
	Enclosure	Indoor Enclosure
Straight Section Length 1 Material S Finish A Knockouts F	Nominal Cross Section	12x12
	Straight Section Length	120
	Material	Steel
	Finish	ANSI 61 Gray Powder Coat Finish
	Knockouts	False
	NEMA Rating	Туре 1

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.

FEATURE TABLE				
ITEM	QTY	DESCRIPTION		
Α	14	Ø.25 MOUNTING HOLE		
В	40	½, ¾ CONC. K.O.		
С	40	3/4, 1 CONC. K.O.		
D	10	1. 1¼ CONC. K.O.		







All dimensions are +/- 1/16". Drawing views are not to scale.

Version:

1

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility, and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.




1212120-GSC1-NK




	Catalog Number	1212120-GSC1-NK
	Marketing Product Description	12x120x12 Screw Cover Wireway Type 1 UL Listed Steel No Knockouts ANSI 61 Gray
	UPC	784572247062
	Length (IN)	120
	Width (IN)	12
	Height (IN)	12
	Weight (LB)	104
	Brand Name	Milbank
	Туре	Lay In Wireway
	Application	Wireway
	Standard	UL Listed
	Cover Type	Screw Cover
	Enclosure	Indoor Enclosure
Straight Section Length 1 Material S Finish A Knockouts F	Nominal Cross Section	12x12
	Straight Section Length	120
	Material	Steel
	Finish	ANSI 61 Gray Powder Coat Finish
	Knockouts	False
	NEMA Rating	Туре 1

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.

FEATURE TABLE				
ITEM	QTY	DESCRIPTION		
Α	14	Ø.25 MOUNTING HOLE		
В	40	½, ¾ CONC. K.O.		
С	40	3/4, 1 CONC. K.O.		
D	10	1. 1¼ CONC. K.O.		







All dimensions are +/- 1/16". Drawing views are not to scale.

Version:

1

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility, and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.