



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



121212GNK 12 X 12 X 12 Wireway

Unity MFG

Catalog Number	121212GNK
Manufacturer	Unity MFG
Description	Wireway, Lay In; Hinged Cover; Length 12 Inch; Width 12 Inch; Height 12 Inch; No Knockout(S); Carbon Steel; Gray Polyester Powder Thermoset Over Phosphatized Surface; Nema 1; Approval UI 870, Csa
Weight per unit	10.0 (lbs/each)
Product Category	Nema Type 1 Wireway & Fittings

Features

Cover Type	HINGED
Knockouts	NO
Material	CARBON STEEL

Material, Color, and Finish

Finish	GRAY POLYESTER POWDER THERMOSET OVER PHOSPHATIZED SURFACE
--------	---

Dimensions and Weight

Height	12 INCH
Height in inch	51869
Length	12 INCH
Length in ft	1 PH
Length in inch	51869
Width	12 INCH
Width in inch	51869

Descriptions

Commodity Description	Nema Type 1 Wireway & Fittings
Description	12 X 12 X 12 WIREWAY
Long Description	WIREWAY, LAY IN; HINGED COVER; LENGTH 12 INCH; WIDTH 12 INCH; HEIGHT 12 INCH; NO KNOCKOUT(S); CARBON STEEL; GRAY POLYESTER POWDER THERMOSET OVER PHOSPHATIZED SURFACE; NEMA 1; APPROVAL UL 870, CSA
Product Type	Hinged Cover Wireway

Manufacturer Information

Brand	Unity MFG
GTIN	00761515106907
Manufacturers Part Number	121212GNK
UPC	761515106907

Taxonomies, Classifications, and Categories

Type	LAY IN
------	--------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

Manufacturer Status Non-Stock

Packaging

Carton 1

Weight Per each 10

Uses, Certifications, and Standards

Approval UL 870, CSA

Enclosure NEMA 1



Type 1 Lay-In Wireway

Application

- Designed to protect electrical wiring where dust, dirt, oil and water are not serious problems. All sections and fittings are fully open on one side so wires and cables can be laid in along an entire run. No pulling through of wires or cables is required.

Construction

- Code gauge low carbon steel
- Concentric knockouts two sides in sizes noted*
- Removable hinged cover standard
- Screw cover flat lid with keyhole slots available
- Complies with UL 870
- Complies with CSA Type 1 (specify CSA label when ordering)

Finish

- Grey polyester powder thermoset over phosphatized surface

GFL

GGFL

GIL (interlocking)
STD without knockouts



- Optional powder coat colors available
- Mill galvanized available - to order use CGFL, standard without knockouts

Specials

- Custom sizes and modifications available

Dividers available

Popular sizes in stock

Add 5% to quantities ordered less than standard cartons

When ordering always specify depth, width and length

Catalog #	NAED#	Size D"xW"xL"	STD		User Price
			CTN	Weight	
252512G	1515 10000	2 1/2 x 2 1/2 x 12	1	2	8.89
25251 8G	1515 10010	2 1/2 x 2 1/2 x 18	1	3	11.50
252524G	1515 10020	2 1/2 x 2 1/2 x 24	1	5	12.78
252536G	1515 10030	2 1/2 x 2 1/2 x 36	1	7	18.89
252548G	1515 10040	2 7/2 x 2 1/2 x 48	1	10	25.56
252560	1515 10050	2 1/2 x 2 1/2 x 60	1	12	31.11
252572G	1515 10060	2 1/2 x 2 1/2 x 72	1	15	42.22
252596G	1515 10070	2 1/2 x 2 1/2 x 96	1	20	55.56
2525120G	1515 10075	27-X272X120	1	25	61.11
*4412G	1515 10080	4x4x12	4	3	8.89
*4418G	1515 10090	4x4x18	2	4	13.33
*4424C	1515 10100	4x4x24	4	6	13.33
*4436C	1515 10110	4x4x36	4	9	18.88
*4448G	1515 10120	4x4x48	4	12	26.66
*4460G	1515 10130	4x4x60	4	15	31.11
4472G	1515 10140	4x4x72	2	18	42.22
4496G	1515 10150	4x4x96	2	24	55.56
441 20G	1515 10160	4x4x120	1	30	66.67
*6612G	1515 10240	6x6x12	2	5	17.77
*6618G	1515 10250	6x6x18	2	7	23.33
*6624C	1515 10260	6x6x24	2	10	23.33
*6636G	1515 10270	6x6x36	2	15	31.66
*6648C	1515 10280	6x6x48	2	20	42.22
*6660C	1515 10290	6x6x60	2	25	47.78
6672G	1515 10300	6x6x72	1	30	61.11
6696G	1515 10310	6x6x96	1	40	93.33
66120	1515 10312	6x6x120	1	50	111.11

Catalog #	NAED#	Size D"xW"xL"	STD		User Price
			CTN	Weight	
881 2C	1515 10400	8x8x12	1	6	30.00
8818C	1515 10410	8x8x18	1	9	44.44
8824C	1515 10420	8x8x24	1	13	44.44
8836C	1515 10430	8x8x36	1	19	68.89
8848C	1515 10440	8x8x48	1	26	80.00
8860C	1515 10450	8x8x60	1	33	93.33
8872C	1515 10460	8x8x72	1	39	120.00
8896C	1515 10470	8x8x96	1	52	177.78
881 20C	1515 10480	8x8x120	1	65	200.00
101012G	1515 10550	10x10x12	1	8	44.44
101024	1515 10560	10x10x24	1	17	65.33
101036C	1515 10570	10x10x36	1	25	100.00
101048C	1515 10580	10x10x48	1	34	120.00
101060C	1515 10590	10x10x60	1	42	140.00
101072C	1515 10600	10x10x72	1	51	180.00
101096	1515 10610	10x10x96	1	68	226.66
1010120C	1515 10620	10x10x120	1	85	280.00
121212G	1515 10690	12x12x12	1	10	46.67
121224G	1515 10700	12x12x24	1	20	85.56
121236G	1515 10710	12x12x36	1	30	122.22
121248G	1515 10720	12x12x48	1	40	150.67
121260G	1515 10730	12x12x60	1	50	170.67
121272G	1515 10740	12x12x72	1	60	213.33
121296G	1515 10750	12x12x96	1	80	248.89
1212120G	1515 10760	12x12x120	1	100	333.33

*with knockouts

Prices subject to change without notice

RO. Box 462321, GARLAND, TEXAS 75046
(972)272-9502 1-800-657-6100
TOLL FREE FAX 1-800-677-JBOX(5269)

