Eaton 12126-4QT

Catalog Number: 12126-4QT

Eaton B-Line series JIC panel enclosure, 12" height, 6" length, 12" width, NEMA 4, Hinged cover, 4QT enclosure, Wall mount, Small single door, External mounting feet, Carbon steel, Seamless poured in-place gasket

Photo is representative

General specifications

Product Name Catalog Number Eaton B-Line series JIC panel enclosure 12126-4QT

UPC Product Length/Depth

782051881820 6 in

Product Height Product Width

12 in 12 in

Product Weight Certifications

11.6 lb CSA C22.2.

NEMA

UL 50



Material/finish

Material

Carbon steel

Wall thickness

16 gauge

Finish color

Painted

Color

ANSI 61 gray

Model

Style

Small single door

Model

4QT enclosure

Cover type

Hinged

Mounting method

Wall

Mounting hole details

External mounting feet

Closure type

Hinged

Special features

Continous piano hinge, panel mount, 1/4 turn latches

Standards

NEMA Rating

Country of origin

US

Resources

Catalogs

Electrical Enclosure Catalog

Specifications and datasheets

Eaton Specification Sheet - 12126-4QT



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia