

Eaton 12126-4XFCHQRC

Catalog Number: 12126-4XFCHQRC

Eaton B-Line series JIC panel enclosure, 13.56" height, 6.36" length, 13.38" width, NEMA 4X, Hinged cover, 4XFCHQRC enclosure, Wall mount, Medium single door, External mounting feet, Fiberglass, Seamless poured in-place gasket



General specifications

Product Name	Catalog Number
Eaton B-Line series JIC panel enclosure	12126-4XFCHQRC
UPC	Product Length/Depth
782051523966	6.36 in
Product Height	Product Width
13.56 in	13.38 in
Product Weight	Certifications
3.2 lb	UL 50
	NEMA
	CSA C22.2.

Material/finish

Material

Fiberglass

Finish color

Unfinished

Color

Gray

Model

Style

Medium single door

Model

4XFCHQRC enclosure

Cover type

Hinged

Mounting method

Wall

Mounting hole details

External mounting feet

Locking provisions

Padlock provision

Closure type

Hinged

Special features

Stainless pull drawn catch

Standards

NEMA Rating

4X

Country of origin

US

Resources

Catalogs

[Electrical Enclosure Catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - 12126-4XFCHQRC](#)