

Eaton 12126-4XSQT

Catalog Number: 12126-4XSQT

Eaton B-Line series JIC panel enclosure, 12" height, 6" length, 12" width, NEMA 4X, Hinged cover, 4XSQT enclosure, Wall mount, Small single door, External mounting feet, 304 stainless steel, Seamless poured in-place gasket



Photo is representative

General specifications

Product Name	Catalog Number
Eaton B-Line series JIC panel enclosure	12126-4XSQT
UPC	Product Length/Depth
782051882117	6 in
Product Height	Product Width
12 in	12 in
Product Weight	Certifications
11.5 lb	UL 50
	CSA C22.2.
	NEMA

Material/finish

Material

304 stainless steel

Wall thickness

16 gauge

Finish color

#4 brushed

Color

Gray

Model

Style

Small single door

Model

4XSQT enclosure

Cover type

Hinged

Mounting method

Wall

Mounting hole details

External mounting feet

Closure type

Hinged

Special features

Continuous piano hinge, panel mount, 1/4 turn latches

Standards

NEMA Rating

4X

Country of origin

US

Resources

Catalogs

[Electrical Enclosure Catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - 12126-4XSQT](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)