Eaton 12126 RHC

Catalog Number: 12126 RHC

Eaton B-Line series Type 3/3R panel enclosures, 12" height, 6" length, 12" width, NEMA 3R, Hinged cover, RHC enclosure, Wall mount, Small single door, 5 bottom knockouts, External mounting feet, Carbon steel

General specifications



Product Name

Eaton B-Line series Type 3/3R panel

enclosures

Product Length/Depth

6 ir

Product Width

12 in

Certifications

UL 50

CSA C22.2.

NEMA

Catalog Number

12126 RHC

UPC

782051145007

Product Height

12 in

Product Weight

11.4 lb



Material/finish

Material

Carbon steel

Wall thickness

16 gauge

Finish color

Painted

Color

ANSI 61 gray

Model

Style

Small single door

Model

RHC enclosure

Cover type

Hinged

Mounting method

Wall

Mounting hole details

External mounting feet

Locking provisions

Padlock provision

Closure type

Hinged

Special features

Rain hood,cont. piano hinge, pull drawn catch

Bottom knockouts

5

Standards

NEMA Rating

3R

Country of origin

US

Resources

Catalogs

Type1-3-3r-enclosure-catalog-section

Specifications and datasheets

Eaton Specification Sheet - 12126 RHC



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia