

Eaton 12128 RTSC NK

Catalog Number: 12128 RTSC NK

Eaton B-Line series Type 3/3R junction boxes, 12" height, 8" length, 12" width, NEMA 3R, Screw cover, RTSC NK enclosure, Surface mounted, Small single door, No knockout, Embossed thru holes, Carbon steel

General specifications



Photo is representative

Product Name	Catalog Number
Eaton B-Line series Type 3/3R junction boxes	12128 RTSC NK
	UPC
	782051336603
Product Length/Depth	Product Height
8 in	12 in
Product Width	Product Weight
12 in	11.5 lb

Certifications

UL 50
CSA C22.2.
NEMA

Material/finish

Material

Carbon steel

Wall thickness

16 gauge

Finish color

Painted

Color

ANSI 61 gray

Model

Style

Small single door

Model

RTSC NK enclosure

Cover type

Screw

Mounting method

Surface

Mounting hole details

Embossed thru holes

Closure type

Flanged cover

Special features

Rain hood, plated screws

Standards

NEMA Rating

3R

Country of origin

US

Resources

Catalogs

[Type1-3-3r-enclosure-catalog-section](#)

Specifications and datasheets

[Eaton Specification Sheet - 12128 RTSC NK](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)