

# Eaton 12128 SCG

Catalog Number: 12128 SCG

Eaton B-Line series Type 3/3R junction boxes, 12" height, 8" length, 12" width, NEMA 3 and 12, Screw cover, SCG enclosure, Surface mounted, Small single door, No mounting provisions, Galvanized steel, Oil-resistant gasket, gasketed screws



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton B-Line series Type 3/3R junction boxes	12128 SCG
	<b>UPC</b>
	782051093377
<b>Product Length/Depth</b>	<b>Product Height</b>
8 in	12 in
<b>Product Width</b>	<b>Product Weight</b>
12 in	16.3 lb

## Certifications

UL 50  
CSA C22.2.  
NEMA

## Material/finish

### Material

Galvanized steel

### Wall thickness

14 gauge

### Finish color

Unfinished

### Color

Gray

## Model

### Style

Small single door

### Model

SCG enclosure

### Cover type

Screw

### Mounting method

Surface

### Mounting hole details

No mounting provisions

## Standards

### NEMA Rating

3

12

### Country of origin

US

## Resources

### Catalogs

[Type1-3-3r-enclosure-catalog-section](#)

### Specifications and datasheets

[Eaton Specification Sheet - 12128 SCG](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)