

# **HT50 HIGH TENSION HACKSAW**

### 50,000 PSI

### HIGHEST TENSION. EVER

Unique I-beam construction allows blade to tension up to 50,000 psi, resulting in fast, straight cuts

### **COMFORTABLE GRIPS**

Rubberized handles allow for confident handling even in wet or cold environments

#### **CONVERT TO A JAB SAW**

Accepts any LENOX reciprocating saw blade to be used as a jab saw

### CONVENIENT BLADE STORAGE

Store up to 5 extra 12" hacksaw blades in the I-Beam

PROD NO BLADE SPECIFICATION

12132HT50 12" (300mm) 24TPI Hacksaw Blade











Tension

Use as a Jab Saw

Stores up to 5 Comfort Grips Blades

# **5012 LOW PROFILE HACKSAW**

## 40,000 PSI

#### HIGH TENSION

Allows blade to tension up to 40,000 PSI, resulting in fast, straight cuts

## FITS INTO TIGHT SPOTS

Low profile tip easily handles close-quarter cuts

### MULTI-PURPOSE

Mount blade at 45 degrees for flush cutting applications

PROD NO	BLADE SPECIFICATION
209205012	12" (300mm) 24TPI Hacksaw Blade



Flush Cutting