
# **INSULATED GROUNDING BUSHINGS**

150° Insulated Grounding Bushings Lay-in Lug Malleable Iron

B42





Catalog #: 1214

#### APPLICATIONS

For use on threaded rigid/IMC conduit to provide a means of grounding conduit through an insulated bushing

#### PRODUCT FEATURES

Lay-in and Feed-thru lug styles provide an easy means of inserting a ground wire Dual rated aluminum grounding lugs may be used with copper or aluminum grounding conductors Insuliner temperature rates at 150 degrees Celsius Malleable iron construction insures mechanical protection for the raceway

Zinc electro plated for corrosion protection

## **UL LISTED**

Standard 514B

## CSA

C22.2 No. 18 GENERAL PRODUCT INFORMATION

1 in. #14 Sol. #4 Str. Trade Size: Min. Grounding Wire Capacity: Max Grounding Wire Capacity:

## DRAWING DIMENSIONS

1-3/4 in. Dimension A: Dimension B 21/32 in. 1 in. - 11-1/2 NPS Dimension C: 31/32 in. Dimension D: Dimension E: Dimension F: 1-1/16 in 3/8 in. Dimension G: 10-32 x 1/4 in.

Dimension H: Dimension I: 10-32 x 1/4 in. 14-28 x 5/8 in.

# PACKAGING Package Type:

Carton Ship Carton Qty.: Product UPC-A Labeled: Weight (Lbs. Per/C): 50 No 13.40 Ship Carton Length (in.): Ship Carton Width (in.): 10.00 5.25 Ship Carton Height (in.): 5.19 Ctn Weight (Lbs.): UPC Number:

6.70 050169012147 12of5 50050169012142