



# 1 in. 150 Degree Rigid/IMC Grounding Bushing, Lay-in-Lug, Insulated

By Raco  
Catalog # 1214



1 in. 150 Degree Rigid/IMC Grounding Bushing, Lay-in-Lug,  
Insulated

\*Representative Image

## Features

- Malleable iron construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Insuliner rated for 150° C
- Grounding Wire Capacity - #14 Sol. - #4 Str.
- UL and CSA Listed
- Available in trade sizes of 1/2 in through 4 in.

## General

Conduit Type	Rigid/IMC
Connector Type	Grounding
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Bushings
Insulation Type	Insulated
Material	Malleable Iron
UPC	050169012147

## Dimensions

Dimensions	0.969 in x 1.75 in x 2.125 in
Height	2.125 in
Length	0.969 in
Trade Size	1 in
Weight	0.134 lb
Width	1.75 in

## Electrical Ratings

Grounding Wire Capacity Maximum	#4 STR
Grounding Wire Capacity Minimum	#14 SOL

## Certifications And Compliance

Certified Listed	<ul style="list-style-type: none"><li>• UL Listed</li><li>• CSA Certified</li></ul>
Industry Standard(s)	UL 514B

## Logistics

Carton Quantity	50
Pallet Quantity	16000

## Product Assets

[Brochures - HCC Products for Solar](#)  
[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC-E195975-1](#)  
[Product Logo - Conduit](#)  
[Sales Drawings - GROUND BUSHING WITH GROUNDING LUG CUS](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
RACO-1214-SPEC-EN | REV 5/2024