

# Manual Controller

12211



Single Pole, Double Throw Switch, 15 amps, 120/277 volts, Ivory.

## features & benefits

- Oversize silver alloy contacts for long life and better heat dissipation.
- Side wired terminals accept #14 #10 AWG copper or copper-clad conductors.
- Fiber terminal insulation barriers standard.
- Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures.
- Bodies, covers, and toggles molded of durable nylon.
- Single Pole-Double Throw and Double Pole-Double Throw.
- Locking Switches supplied with one 1498-NT key.
- Normally open.



# specifications

#### **General Info**

Color: Ivory

Type: Maintained Contact Number Of Poles: 1

Special Features: Two Circuit

#### **Listing Agencies/Third Party Information**

CSA Listing Info: Yes CUL Listing No: No

cULus: No cURus: No Federal Spec: No UL Listing No: Yes UN SPS C: 39121507

UR: No

#### **Dimensions**

Depth U S: 1.469" Height U S: 3.281" Weight: 0.24487 Width U S: 1.5"

#### **Technical Information**

Amps: 15 Amp Volts: 120/277VAC Volts A C: 120/277

### **Buy American Act Compliance**

Country of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant