

Specifications



Eaton 1221V

Eaton construction grade toggle switch, #14-10 AWG, 20A, Industrial, Flush mount, 120/277V, Back and side, Screw, Ivory, Single-Pole, Single-Pole, Brass, Polycarbonate

General specifications

PRODUCT NAME	Eaton construction grade toggle switch
CATALOG NUMBER	1221V
UPC	032664735677
PRODUCT LENGTH/DEPTH	1.31 in
PRODUCT HEIGHT	3.28 in
PRODUCT WIDTH	0.88 in
PRODUCT WEIGHT	0.001 lb
CERTIFICATIONS	UL cULus Listed NOM
PRODUCT TYPE	Construction grade toggle switch



Powering Business Worldwide

Electrical Ratings

AMPERAGE RATING	20A
TORQUE RATING	14 lbf-inch
VOLTAGE RATING	120/277 V
WIRING METHOD	Back and side

Material Specifications

COLOR	Ivory
MATERIAL	Polycarbonate
TERMINAL ENCLOSURE MATERIAL	Brass

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - 1221V](#)

[Heavy-duty industrial grade AC toggle switch spec sheet](#)

Installation

MOUNTING METHOD	Flush
------------------------	-------

Product Specifications

ALLOWABLE WIRE SIZE	#14-10 AWG
APPLICATION	Industrial
CONNECTOR TYPE	Screw
NUMBER OF POLES	Single-pole
SWITCH TYPE	Single-pole
TYPE	Toggle switch

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications



Eaton 1221V

Eaton construction grade toggle switch, #14-10 AWG, 20A, Industrial, Flush mount, 120/277V, Back and side, Screw, Ivory, Single-Pole, Single-Pole, Brass, Polycarbonate

General specifications

PRODUCT NAME	Eaton construction grade toggle switch
CATALOG NUMBER	1221V
UPC	032664735677
PRODUCT LENGTH/DEPTH	1.31 in
PRODUCT HEIGHT	3.28 in
PRODUCT WIDTH	0.88 in
PRODUCT WEIGHT	0.001 lb
CERTIFICATIONS	UL cULus Listed NOM
PRODUCT TYPE	Construction grade toggle switch



Powering Business Worldwide

Electrical Ratings

AMPERAGE RATING	20A
TORQUE RATING	14 lbf-inch
VOLTAGE RATING	120/277 V
WIRING METHOD	Back and side

Material Specifications

COLOR	Ivory
MATERIAL	Polycarbonate
TERMINAL ENCLOSURE MATERIAL	Brass

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - 1221V](#)

[Heavy-duty industrial grade AC toggle switch spec sheet](#)

Installation

MOUNTING METHOD	Flush
------------------------	-------

Product Specifications

ALLOWABLE WIRE SIZE	#14-10 AWG
APPLICATION	Industrial
CONNECTOR TYPE	Screw
NUMBER OF POLES	Single-pole
SWITCH TYPE	Single-pole
TYPE	Toggle switch

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

