

# Specifications

## Eaton 1221V

Eaton construction grade toggle switch, #14-10 AWG, 20A, Industrial, Flush mount, 120/277V, Back and side, Screw, Ivory, Single-Pole, Single-Pole, Brass, Polycarbonate

### General specifications

<b>PRODUCT NAME</b>	Eaton construction grade toggle switch
<b>CATALOG NUMBER</b>	1221V
<b>UPC</b>	032664735677
<b>PRODUCT LENGTH/DEPTH</b>	1.31 in
<b>PRODUCT HEIGHT</b>	3.28 in
<b>PRODUCT WIDTH</b>	0.88 in
<b>PRODUCT WEIGHT</b>	0.001 lb
<b>CERTIFICATIONS</b>	UL cULus Listed NOM
<b>PRODUCT TYPE</b>	Construction grade toggle switch



Powering Business Worldwide

## Electrical Ratings

<b>AMPERAGE RATING</b>	20A
<b>TORQUE RATING</b>	14 lbf-inch
<b>VOLTAGE RATING</b>	120/277 V
<b>WIRING METHOD</b>	Back and side

## Material Specifications

<b>COLOR</b>	Ivory
<b>MATERIAL</b>	Polycarbonate
<b>TERMINAL ENCLOSURE MATERIAL</b>	Brass

## Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - 1221V](#)

[Heavy-duty industrial grade AC toggle switch spec sheet](#)

## Installation

<b>MOUNTING METHOD</b>	Flush
------------------------	-------

## Product Specifications

<b>ALLOWABLE WIRE SIZE</b>	#14-10 AWG
<b>APPLICATION</b>	Industrial
<b>CONNECTOR TYPE</b>	Screw
<b>NUMBER OF POLES</b>	Single-pole
<b>SWITCH TYPE</b>	Single-pole
<b>TYPE</b>	Toggle switch

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

