

# Eaton 1233-BOX

Catalog Number: 1233-BOX

Eaton power device receptacle, #12 - 4 AWG, 30A, Flush, 125V, Back, Brown, NEMA 5-30R, Two-pole, Three-wire, Two-pole, three-wire, grounding, Screw, Glass-filled nylon, Power, Used with S41



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton power device receptacle	1233-BOX
<b>UPC</b>	<b>Product Length/Depth</b>
032664306204	3.88 in
<b>Product Height</b>	<b>Product Width</b>
2.25 in	2.94 in
<b>Product Weight</b>	<b>Compliances</b>
0.38 lb	RoHS Compliant
	NAFTA
<b>Certifications</b>	
UL Listed	
NOM	
CSA Certified	

## Product specifications

### Color

Brown

### Wiring method

Back

### Material

Glass filled nylon

### Mounting method

Flush

### Allowable wire size

#12-4 AWG

### Amperage Rating

30A

### Number Of Poles

Two-pole

### NEMA configuration

5-30R

### Used with

S41

### Design type

Receptacle

### Connection type

Screw

### Style

Power

### Number of wires

3

### Receptacle type

Two-pole, three-wire, grounding

### Voltage rating

125 V

### Torque rating

25 lbf-inch

## Resources

### Brochures

[Flush mount receptacles sell sheet](#)

### Catalogs

[Arrow Hart Buyers Guide Section B](#)

### Specifications and datasheets

[Eaton Specification Sheet - 1233-BOX](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)