

### Industrial straight blade power devices features & benefits

Rugged high-strength thermoplastic construction

Neoprene gasket seals around cord for added terminal protection from external elements



Plug

Unique internal clamp design secures cord during assembly, reducing installation time



Connector

Tapered cord grip cover reduces cord snags



Angled plug versions have 4 possible positions for maximum convenience



Broad selection of flanged inlets accept #12 AWG to #4 AWG conductors



Quick-drive stainless steel assembly screws provide corrosion resistance and speed installation time



Variety of 30A, 50A and 60A configurations available