

Specifications



Photo is representative



Eaton 1242-7B-BOX

Eaton toggle switch, #14-10 AWG, 15A, Residential, Wall, 120V, Side and push, Grounding, Brown, Four-way, Polycarbonate

General specifications

PRODUCT NAME	Eaton toggle switch
CATALOG NUMBER	1242-7B-BOX
UPC	032664734960
PRODUCT LENGTH/DEPTH	1.31 in
PRODUCT HEIGHT	3.28 in
PRODUCT WIDTH	0.88 in
PRODUCT WEIGHT	0.001 lb
COMPLIANCES	NAFTA
CERTIFICATIONS	cULus Listed
PRODUCT TYPE	Toggle switch



Powering Business Worldwide

Product specifications

SPECIAL FEATURES	Box
TYPE	Toggle switch
AMPERAGE RATING	15A
VOLTAGE RATING	120 V
NUMBER OF POLES	Two-pole
APPLICATION	Residential
WIRING METHOD	Side and push
SWITCH TYPE	Four-way
MOUNTING METHOD	Wall
CONNECTOR TYPE	Grounding
MATERIAL	Polycarbonate
NUMBER OF WAYS	Four-way
ALLOWABLE WIRE SIZE	#14-10 AWG
TORQUE RATING	14 lbf-inch
COLOR	Brown

Resources

SPECIFICATIONS AND
DATASHEETS

[Eaton Specification Sheet -
1242-7B-BOX](#)

[Residential grade toggle
switches spec sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the
latest product and support
information.

