



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3448 Sherwood Way
76901-0000, TX San Angelo
Phone: 325-944-7321
Fax: 325-944-1579



1250GRY SW Moment Control 15A 120/277V (SPDT) Gy

Pass & Seymour/Legrand

Catalog Number	1250GRY
Manufacturer	Pass & Seymour/Legrand
Description	Single-Pole, Double-Throw Switch. 15A, 120/277VAC Rating. Tested to 3 Amps, 24VDC Rating.
Weight per unit	0.2750 (lbs/each)
Product Category	Manual Motor Switches & Accy.

Features

amperage rating	15
Contact Configuration	NO
Contact Rating	15amp, 120/277vac
insulation	Bare
Material	Nylon
Mounting Type	Box
Poles	1
Switch Type	Momentary
throw type	Double Throw
Voltage	120/277 V
Voltage Rating	120/277
Wattage	1
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Color	Gray
Finish	Matte

Dimensions and Weight

Size	3.3"
------	------

Descriptions

Description	SW MOMENT CONTROL 15A 120/277V (SPDT) GY
extra long description	P&S 1250GRY SW MOMENT CNTRL 15A 12
Features	Single-Pole, Double-Throw Switch. 15A, 120/277VAC rating. Tested to 3 Amps, 24Vdc rating.
Long Description	Single-Pole, Double-Throw Switch. 15A, 120/277VAC rating. Tested to 3 Amps, 24Vdc rating.
Product Type	SW Moment CNTRL 15A 120/277V (SPDT) Gy
Special Features	Oversized silver alloy contacts, side wired, can be mounted in standard device box\



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3448 Sherwood Way
76901-0000, TX San Angelo
Phone: 325-944-7321
Fax: 325-944-1579

Manufacturer Information

Brand	Pass & Seymour/Legrand
GTIN	00785007039207
Manufacturers Part Number	1250-GRY
UPC	785007039207

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	SWITCH

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	1
Package	10
Weight Per each	0.275

Uses, Certifications, and Standards

Application	Industrial
Enclosure	Box or NEMA 1 sheet steel
Mounting	WALL
standard	CULUS, UL, CSA, UL listed