

Manual Controller

1250L



Single Pole, Double Throw Manual Control Switch, 15 amps, 120/277 volts, Locking.

features & benefits

Oversize silver alloy contacts for long life and better heat dissipation. Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors. Fiber terminal insulation barriers standard. Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures. Bodies, covers, and toggles molded of durable nylon. Single Pole-Double Throw and Double Pole-Double Throw. Locking Switches supplied with one 1498-NT key. Normally open.



specifications

General Info

Type: Momentary Contact
Number Of Poles: 1
Special Features: Three Position

Listing Agencies/Third Party Information

CSA Listing Info: Yes
CUL Listing No: No
cULus: No
cURus: No
Federal Spec: No
UL Listing No: Yes
UN SPS C: 39121507
UR: No

Dimensions

Depth U S: 1.469"
Height U S: 3.281"
Weight: 0.26216
Width U S: 1.5"

Technical Information

Amps: 15 Amp
Volts: 120/277VAC
Volts A C: 120/277

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant