



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

720 S Lewis Ln
78552-0000, TX Harlingen
Phone: 956-622-4123
Fax: 956-622-4124



1250L Switch Moment Control 15A 120/277V Lock Gy

Pass & Seymour/Legrand

Catalog Number	1250L
Manufacturer	Pass & Seymour/Legrand
Description	Locking Manual Controller, Single-Pole, Double-Throw Switch. 15A, 120/277VAC Rating, Tested to 3A, 24VDC Rating.
Weight per unit	0.2750 (lbs/each)
Product Category	Manual Motor Switches & Accy.

Features

amperage rating	15
Contact Configuration	NO
Contact Rating	15amp, 120/277vac
indoor/outdoor	Indoor
insulation	Bare
Load Rating	15 A @ 120/277 VAC
Load Type	Incandescent, Halogen, Xenon, LED, Fluorescent, CFL, Universal
Material	Thermoplastic
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	1.0
Poles	1
Switch Type	Locking
throw type	Double Throw
Voltage	120/277 V
Voltage Rating	120/277
Wall Plate Included	NO
Wattage	1
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Color	Locking
Finish	Matte

Dimensions and Weight

Size	3.3"
------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

720 S Lewis Ln
78552-0000, TX Harlingen
Phone: 956-622-4123
Fax: 956-622-4124

Descriptions

Description	SWITCH MOMENT CONTROL 15A 120/277V LOCK GY
extra long description	P&S 1250L SW MOMENT CNTRL 15A 120/
Features	Durable
Long Description	Locking Manual Controller, Single-Pole, Double-Throw Switch. 15A, 120/277VAC rating, Tested to 3A, 24VDC rating.
Product Type	SW Moment CNTRL 15A 120/277V Lock Gy
Special Features	Oversized silver alloy contacts, side wired, can be mounted in standard device box\

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007125023
Manufacturers Part Number	1250-L
UPC	785007125023

Taxonomies, Classifications, and Categories

Category Description	Residential plates
Type	Manual Controller

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	1
Package	10
Weight Per each	0.275

Uses, Certifications, and Standards

Application	Industrial
Enclosure	Box or NEMA 1 sheet steel
Mounting standard	WALL CSA, UL, CULUS, UL listed