



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

10440 Airline Highway
70816-0000, LA Baton Rouge
Phone: 225-292-7746
Fax: 225-292-7840



1250W Manual Control 15A SPDT Mmnlry W/WH Tog

Pass & Seymour/Legrand

Catalog Number	1250W
Manufacturer	Pass & Seymour/Legrand
Description	Single-Pole, Double-Throw Switch. 15A, 120/277VAC Rating. Tested to 3 Amps, 24VDC Rating.
Weight per unit	0.2750 (lbs/each)
Product Category	Manual Motor Switches & Accy.

Features

action	SP, DT
actuator	Toggle
amperage rating	15
Contact Rating	15Amp, 120/277V
insulation	Bare
Material	Nylon
Mounting Type	Box
Poles	1
Switch Type	Momentary
throw type	Double Throw
Voltage	120/277 V
Voltage Rating	120/277
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Color	White
Finish	Matte

Dimensions and Weight

Size	3.3"
------	------

Descriptions

Description	MANUAL CONTROL 15A SPDT MMNLRY W/WH TOG
extra long description	P&S 1250W MAN CTRLR 15A SPDT MMNLRY
Features	Single-Pole, Double-Throw Switch. 15A, 120/277VAC rating. Tested to 3 Amps, 24Vdc rating.
Long Description	Single-Pole, Double-Throw Switch. 15A, 120/277VAC rating. Tested to 3 Amps, 24Vdc rating.
Product Type	Man CTRLR 15A SPDT Mmnlry W/WH Tog
Special Features	Side wire terminals, Fiber Terminal insulation barrier\



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

10440 Airline Highway
70816-0000, LA Baton Rouge
Phone: 225-292-7746
Fax: 225-292-7840

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007125146
Manufacturers Part Number	1250-W
UPC	785007125146

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	SWITCH

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	1
Package	10
Weight Per each	0.275

Uses, Certifications, and Standards

Application	Industrial
Mounting standard	WALL UL, CSA, CULUS, UL Listed