

# Eaton 1252

Catalog Number: 1252

Eaton power device receptacle, #12 - 4 AWG, 50A, Surface, 250V, Back and bottom, Black, NEMA 6-50R, Two-pole, Three-wire, Two-pole, three-wire, grounding, Glass-filled nylon, Power



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton power device receptacle	1252
<b>UPC</b>	<b>Product Length/Depth</b>
032664306501	2.25 in
<b>Product Height</b>	<b>Product Width</b>
9 in	5 in
<b>Product Weight</b>	<b>Compliances</b>
0.685 lb	RoHS Compliant
<b>Certifications</b>	
UL Listed	
NOM	
CSA Certified	

## Product specifications

### Color

Black

### Wiring method

Back and bottom

### Material

Glass filled nylon

### Mounting method

Surface

### Allowable wire size

#12-4 AWG

### Amperage Rating

50 A

### Number Of Poles

Two-pole

### NEMA configuration

6-50R

### Design type

Receptacle

### Style

Power

### Number of wires

3

### Receptacle type

Two-pole, three-wire, grounding

### Voltage rating

250 V

### Torque rating

25 lbf-inch

## Resources

### Brochures

[Flush mount receptacles sell sheet](#)

[Wiring Devices Buyer's Guide](#)

### Catalogs

[Residential Buyers Guide Section B](#)

### Specifications and datasheets

[Eaton Specification Sheet - 1252](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)