

Eaton 1253-BOX

Catalog Number: 1253-BOX

Eaton power device receptacle, #12 - 4 AWG, 50A, Flush, 125V, Back, Black, NEMA 5-50R, Two-pole, Three-wire, Two-pole, three-wire, grounding, Screw, Glass-filled nylon, Power, Used with A41

General specifications



Product Name

Eaton power device receptacle

Catalog Number

1253-BOX

UPC

032664306600

Product Length/Depth

3.88 in

Product Height

2.25 in

Product Width

2.94 in

Product Weight

0.35 lb

Compliances

RoHS Compliant
NAFTA

Certifications

CSA Certified
UL Listed



Powering Business Worldwide

Product specifications

Color

Black

Wiring method

Back

Material

Glass filled nylon

Mounting method

Flush

Allowable wire size

#12-4 AWG

Amperage Rating

50 A

Number Of Poles

Two-pole

NEMA configuration

5-50R

Used with

A41

Design type

Receptacle

Connection type

Screw

Style

Power

Number of wires

3

Receptacle type

Two-pole, three-wire, grounding

Voltage rating

125 V

Torque rating

25 lbf-inch

Resources

Brochures

[Flush mount receptacles sell sheet](#)

Catalogs

[Arrow Hart Buyers Guide Section B](#)

Specifications and datasheets

[Eaton Specification Sheet - 1253-BOX](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)