

Non-Metallic Fixture Whips

Non-Metallic Liquidtight Conduit - Type LFNC-B



Conduit

- Type LFNC-B, Nonmetallic Liquidtight

Conductors

- Stranded Copper

Conductor Insulation

- THHN/THWN

Neutral Conductors

- White 120/208V

Grounding

- Insulated Green Copper Grounding Conductor

Maximum Voltage Rating


- 600V

Maximum Temperature Rating

- 80°C (Dry); 60°C (Wet)

Reference & Rating

- UL 83, 514B and 1660, File Reference E96572
- NEC® 250, 356, 410, 430, 440
- Made in USA of US and/or imported materials



Conductor AWG (Color)	Conduit Trade Size x Length (ft)	Product Code	Units Per Package
10-3 Stranded (Black, Red, Green)	½ x 4	8014	10 per Box
10-3 Stranded (Black, Red, Green)	½ x 6	8015	10 per Box
8-3 Stranded (Black, Red, Green)	¾ x 4	8016	10 per Box
8-3 Stranded (Black, Red, Green)	¾ x 6	8017	8 per Box
10-3 Stranded (Black, Red, Green)	½ x 4	8021	20 Bulk
10-3 Stranded (Black, Red, Green)	½ x 6	8022	15 Bulk
8-3 Stranded (Black, Red, Green)	¾ x 4	8023	10 Bulk
8-3 Stranded (Black, Red, Green)	¾ x 6	8024	10 Bulk

Note: All Whips come with one straight non-metallic liquidtight connector and one 90 angle non-metallic liquidtight connector. Other conductor colors available by special request.

Non-Metallic Fixture Whips

Non-Metallic Liquidtight Conduit - Type LFNC-B



Conduit

- Type LFNC-B, Nonmetallic Liquidtight

Conductors

- Stranded Copper

Conductor Insulation

- THHN/THWN

Neutral Conductors

- White 120/208V

Grounding

- Insulated Green Copper Grounding Conductor

Maximum Voltage Rating


- 600V

Maximum Temperature Rating

- 80°C (Dry); 60°C (Wet)

Reference & Rating

- UL 83, 514B and 1660, File Reference E96572
- NEC® 250, 356, 410, 430, 440
- Made in USA of US and/or imported materials



Conductor AWG (Color)	Conduit Trade Size x Length (ft)	Product Code	Units Per Package
10-3 Stranded (Black, Red, Green)	½ x 4	8014	10 per Box
10-3 Stranded (Black, Red, Green)	½ x 6	8015	10 per Box
8-3 Stranded (Black, Red, Green)	¾ x 4	8016	10 per Box
8-3 Stranded (Black, Red, Green)	¾ x 6	8017	8 per Box
10-3 Stranded (Black, Red, Green)	½ x 4	8021	20 Bulk
10-3 Stranded (Black, Red, Green)	½ x 6	8022	15 Bulk
8-3 Stranded (Black, Red, Green)	¾ x 4	8023	10 Bulk
8-3 Stranded (Black, Red, Green)	¾ x 6	8024	10 Bulk

Note: All Whips come with one straight non-metallic liquidtight connector and one 90 angle non-metallic liquidtight connector. Other conductor colors available by special request.