

AFC Nonmetallic Whips Type UL

Conduit

Type LFNC-B, Nonmetallic Liquidtight

Conductors

THHN/THWN 8 & 10 AWG Stranded

Maximum Temperature Rating

90°C (Dry); 75°C (Wet)

Grounding

NEC® 250.118(1)

Maximum Voltage Rating

600V

References & Ratings

- UL 83, 1660 and 514B, File Reference E96572
- NEC® 410, 430, 440, 250, 356



Product Core	Trade Size (in)	Length (ft)	No. of Cond.	AWG (Cond. Size)	Put Up
Non-metallic Liquidtight Whips (Standard Configurations)					
8014	1/2"	4'	3	10	10 per box
8015	1/2"	6'	3	10	10 per box
8016	3/4"	4'	3	8	10 per box
8017	3/4"	6'	3	8	8 per box
8021	1/2"	4'	3	10	20 bulk
8022	1/2"	6'	3	10	15 bulk
8023	3/4"	4'	3	8	10 bulk
8024	3/4"	6'	3	8	10 bulk

Whips come with Black, Red, Green THHN/THWN conductors.

Other conductor colors available by special request.

All whips come with one straight non-metallic liquidtight connector and one 90° angle non-metallic liquidtight connector.

Pack N Roll™ Type MC and AC Cable Dispenser

Description

Our patented heavy duty cable accessory enables electrical contractors to perform remodel and small construction/service projects with ease.

Catalog Number

9989-BE

Net Weight

16.4 Lbs

Dimensions

19" Diameter
12-13/16" High

Capacity

250 Ft Coils

- Fast and Easy to Pull without any Tangles
- Reduces Cable Memory
- Stackable
- Eliminates Scrap
- Keeps Cable Organized, Neat and Clean
- Prevents Cable Damage

*Accommodates the majority of AFC's coil products

