

# Specifications



## Eaton 1301-7B

Eaton toggle switch, #14-10 AWG, 15A, Flush, 120V, Side and push, Screw, Brown, Load type: Motor Control, Fan, LED, Incandescent, ELV, MLV, CFL, Fluorescent, Halogen, Single-Pole, Single-Pole, Polycarbonate

### General specifications

<b>PRODUCT NAME</b>	Eaton toggle switch
<b>CATALOG NUMBER</b>	1301-7B
<b>UPC</b>	032664149108
<b>PRODUCT LENGTH/DEPTH</b>	1.31 in
<b>PRODUCT HEIGHT</b>	3.28 in
<b>PRODUCT WIDTH</b>	0.88 in
<b>PRODUCT WEIGHT</b>	0.102 lb
<b>COMPLIANCES</b>	RoHS Compliant NAFTA
<b>CERTIFICATIONS</b>	cULus Listed NOM
<b>PRODUCT TYPE</b>	Toggle switch



Powering Business Worldwide

## Product specifications

**TYPE** Toggle switch

**AMPERAGE RATING** 15A

**VOLTAGE RATING** 120 V

**NUMBER OF POLES** Single-pole

**APPLICATION** Residential

**WIRING METHOD** Side and push

**SWITCH TYPE** Single-pole

**MOUNTING METHOD** Flush

**CONNECTOR TYPE** Screw

**LOAD TYPE** MLV  
INC  
ELV  
FLR  
Fan  
HAL  
CFL  
Motor Control  
LED

**MATERIAL** Polycarbonate

**ALLOWABLE WIRE SIZE** #14-10 AWG

**TORQUE RATING** 14 lbf-inch

**COLOR** Brown

## Resources

SPECIFICATIONS AND DATASHEETS [Eaton Specification Sheet - 1301-7B](#)  
[Residential grade toggle switches spec sheet](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications



## Eaton 1301-7B

Eaton toggle switch, #14-10 AWG, 15A, Flush, 120V, Side and push, Screw, Brown, Load type: Motor Control, Fan, LED, Incandescent, ELV, MLV, CFL, Fluorescent, Halogen, Single-Pole, Single-Pole, Polycarbonate

### General specifications

<b>PRODUCT NAME</b>	Eaton toggle switch
<b>CATALOG NUMBER</b>	1301-7B
<b>UPC</b>	032664149108
<b>PRODUCT LENGTH/DEPTH</b>	1.31 in
<b>PRODUCT HEIGHT</b>	3.28 in
<b>PRODUCT WIDTH</b>	0.88 in
<b>PRODUCT WEIGHT</b>	0.102 lb
<b>COMPLIANCES</b>	RoHS Compliant NAFTA
<b>CERTIFICATIONS</b>	cULus Listed NOM
<b>PRODUCT TYPE</b>	Toggle switch



Powering Business Worldwide

## Product specifications

**TYPE** Toggle switch

**AMPERAGE RATING** 15A

**VOLTAGE RATING** 120 V

**NUMBER OF POLES** Single-pole

**APPLICATION** Residential

**WIRING METHOD** Side and push

**SWITCH TYPE** Single-pole

**MOUNTING METHOD** Flush

**CONNECTOR TYPE** Screw

**LOAD TYPE** MLV  
INC  
ELV  
FLR  
Fan  
HAL  
CFL  
Motor Control  
LED

**MATERIAL** Polycarbonate

**ALLOWABLE WIRE SIZE** #14-10 AWG

**TORQUE RATING** 14 lbf-inch

**COLOR** Brown

## Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - 1301-7B](#)

[Residential grade toggle switches spec sheet](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

