

Specifications



Eaton 1301-7B

Eaton toggle switch, #14-10 AWG, 15A, Flush, 120V, Side and push, Screw, Brown, Load type: Motor Control, Fan, LED, Incandescent, ELV, MLV, CFL, Fluorescent, Halogen, Single-Pole, Single-Pole, Polycarbonate

General specifications

PRODUCT NAME	Eaton toggle switch
CATALOG NUMBER	1301-7B
UPC	032664149108
PRODUCT LENGTH/DEPTH	1.31 in
PRODUCT HEIGHT	3.28 in
PRODUCT WIDTH	0.88 in
PRODUCT WEIGHT	0.102 lb
COMPLIANCES	RoHS Compliant NAFTA
CERTIFICATIONS	cULus Listed NOM
PRODUCT TYPE	Toggle switch

Product specifications

TYPE	Toggle switch
AMPERAGE RATING	15A
VOLTAGE RATING	120 V
NUMBER OF POLES	Single-pole
APPLICATION	Residential
WIRING METHOD	Side and push
SWITCH TYPE	Single-pole
MOUNTING METHOD	Flush
CONNECTOR TYPE	Screw
LOAD TYPE	MLV INC ELV FLR Fan HAL CFL Motor Control LED
MATERIAL	Polycarbonate
ALLOWABLE WIRE SIZE	#14-10 AWG
TORQUE RATING	14 lbf-inch
COLOR	Brown

Resources

SPECIFICATIONS AND
DATASHEETS

[Eaton Specification Sheet -
1301-7B](#)

[Residential grade toggle
switches spec sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the
latest product and support
information.

