



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 130C112X30 Linerless Rubber Splicing Tape, 1-1/2" X 30', BK *Minnesota Mining (3M)*

|                  |  |
|------------------|--|
| Catalog Number   | 130C112X30   |
| Manufacturer     | Minnesota Mining (3M)  |
| Description      | Linerless Rubber Tape, Black, 7.5 LB/In Tensile Strength, 850 % Elongation At Break, +194 °F Operating Temperature, 30 FT Length, 1.5 In Width, 30 Mil Thickness, 5 Yr Shelf Life, 0.93 LB |
| Weight per unit  | 0.0775 (lbs/each)  |
| Product Category | Markers & Marking Tapes - Tape   |

### Descriptions

|                        |  |
|------------------------|--|
| Description            | LINERLESS RUBBER SPLICING TAPE, 1-1/2" X 30', BK |
| extra long description | 3M 7000006086 Scotch® Linerless Rub              |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Scotch         |
| GTIN                      | 00054007417187 |
| Manufacturers Part Number | 130C-1.5X30FT  |
| UPC                       | 054007417187   |

### Taxonomies, Classifications, and Categories

|                      |                                     |
|----------------------|-------------------------------------|
| Category Description | TAPE                                |
| Type                 | linerless Ethylene Propylene Rubber |

### Packaging

|                 |        |
|-----------------|--------|
| Carton          | 12     |
| Weight Per each | 0.0775 |

### Uses, Certifications, and Standards

|          |                                      |
|----------|--------------------------------------|
| standard | ASTM D-4388 type 1, 2 & 3 HH-I-3825B |
|----------|--------------------------------------|