

# Eaton 13100AQD07

Catalog Number: 13100AQD07

Eaton Moeller® series E58 Diffuse reflective sensor, Sn=610mm, 4L, 10-30VDC, NPN, PNP, M18, insulated material, M12

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton Moeller® series E58 Diffuse reflective sensor	13100AQD07
	<b>Model Code</b>
	13100AQD07
<b>UPC</b>	<b>EAN</b>
782113843551	4015081323746
<b>Product Length/Depth</b>	<b>Product Height</b>
158.75 mm	50.8 mm
<b>Product Width</b>	<b>Product Weight</b>
133.35 mm	0.091 kg
<b>Warranty</b>	<b>Certifications</b>
3 year	UL Recognized
	cUL Recognized
	CE
	UL
	CSA Class No.: 3211-07
	CSA File No.: 50513
	UL Category Control No.: NRKH, NRKH7
	UL 508
	CSA
	CSA-C22.2 No. 14
	IEC/EN 60947-5-2
	UL File No.: E117028

## defaultTaxonomyAttributeLabel

### Type

Optical sensors

### Contact Rating

100 mA PNP, 250 mA NPN at 10-30 Vdc

### Features

Straight beam

### Electric connection type

Plug-in connection

### Enclosure material

Polyurethane foam (RIM)

Plastic

### Enclosure type

Cylinder, screw-thread

### Operating mode

Switching principle: Adjustable bright/dark switching

### Connection

M12

### Contact configuration

NPN and PNP open collector

### Explosion safety category for dust

None

### Sensor type

Diffuse reflective

### Explosion safety category for gas

None

### Functions

Reflected-light beam

Protection against polarity reversal

Short-circuit protection

### Voltage type

DC

### Wire size

22

### Connection type

Plug-in connection M12 x 1

4-wire

## Resources

### Brochures

Comet series - Photoelectric sensors

### Catalogs

Eaton's Volume 8—Sensing Solutions

Product Range Catalog Sensors – products, basic information, applications

### Certification reports

DA-DC-00004652.pdf

DA-DC-00004657.pdf

### Drawings

eaton-proximity-switches-dimensions-003.eps

eaton-proximity-switches-dimensions-002.eps

eaton-proximity-switches-3d-drawing-007.eps

### Installation instructions

IL05305002Z

### mCAD model

DA-CS-90\_28267\_104

DA-CD-90\_28267\_104

### Specifications and datasheets

Eaton Specification Sheet - 13100AQD07

Input voltage

10-30 Vdc

Cable sheath material

Polyvinyl chloride (PVC)

Light type

Infrared light

Degree of protection

IP67

NEMA 6

Interface type

Other

LED indicator

Output ON

Status indication of Switching state: Red LED

Switch function type

Other

Load current

Max. 250 mA (Ie, NPN, 120 > 50°C)

Max. 100 mA (Ie, PNP)

Laser protection class

None

Operation agent-safety class

Safety class 2

Shock resistance

100 g, Mechanical, Shock duration 3 ms

Optical surface material

Plastic

Output current (mA) - max

250 mA

Output current at protected output - max

0 mA

Rated control supply voltage (Us) at AC, 50 Hz - max

0 V

Rated control supply voltage (Us) at AC, 50 Hz - min

0 V

Rated control supply voltage (Us) at AC, 60 Hz - max

0 V

Rated control supply voltage (Us) at AC, 60 Hz - min

0 V

Rated control supply voltage (Us) at DC - max

30 V

Rated control supply voltage (Us) at DC - min

10 V

Rated switching distance (Sn)

610 mm

Reflector distance - min

0 mm

Sensor height

0 mm

Sensor length

56 mm

Switching distance - max

610 mm

Switching voltage of OSSD at state high

0 V

Transmission range of the safety field

0 m

Voltage rating - max

30 V

Safety type (IEC 61496-1)

1

Switching frequency

500 Hz

Sensing mode

Light-/dark switching

Switching output type

PNP/NPN

Sensor material

Insulated material

Wavelength of the sensor

0 nm

Width sensor

0 mm

Accessories

Can be expanded with fibre optic cable.

Product category

Comet Series

Number of pins

4

Protection

Auto reset short circuit

Response time

1 ms

Maximum DC current

100 mA PNP, 250 mA NPN

Ambient operating temperature - max

70 °C

Ambient operating temperature - min

-40 °C

Diameter sensor

18 mm

Light dot size

0 mm<sup>2</sup>

Number of contact energized outputs with signalling function

0

Number of outputs (protected contact energized)

0

Number of outputs (protected semiconductor)

0

Number of outputs (semiconductor with signaling function)

2

Operating distance - max

0 mm

Operating distance - min

0 mm

Operating temperature - max

158 °F

Operating temperature - min

-40 °F

Operational current (I<sub>b</sub>) in the switched state at 24 V DC

30 A

Environmental rating

NEMA 1, NEMA 3, NEMA 4, NEMA 4X, NEMA 6, NEMA 12,  
NEMA 13, IP69K

Adjustment type

Manual adjustment



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)