



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



13101AQD07 4" PPRX Conn Version DC

Eaton Corp

Catalog Number	13101AQD07
Manufacturer	Eaton Corp
Description	Eaton Comet 18MM Tubular Photoelectric Sensor, Perfect Prox Photoelectric Sensor, Back Ground Suppression, 4 In Range, Forward Viewing, Output On, M12, 100 Ma PNP, 250 Ma NPN At 10-30 VDC, 4 Pin, NPN and PNP Open Collector, 10-30 VDC
Weight per unit	0.6700 (lbs/each)
Product Category	Photoelectric Sensors

Features

connection	M12
dimensions	2.0600 IN X 0.4700 IN X 0.7100 IN

Descriptions

Description	4" PPRX CONN VERSION DC
extra long description	ETN 13101AQD07 4" PPRX CONN VERSION
Features	Eaton's Comet Series Photoelectric Sensors is a complete line of high performance, 18 mm tubular sensors with a variety of models and modes to solve virtually any sensing problem.
Long Description	Eaton Comet 18mm tubular photoelectric sensor, Perfect Prox Photoelectric Sensor, Back Ground Suppression, 4 in range, Forward Viewing, Output ON, M12, 100 mA PNP, 250 mA NPN at 10-30 Vdc, 4 pin, NPN and PNP open collector, 10-30 Vdc
Product Type	4" PPRX Conn Version DC

Manufacturer Information

Brand	Eaton
GTIN	00782113938318
Manufacturers Part Number	13101AQD07
UPC	782113938318

Taxonomies, Classifications, and Categories

Category Description	PROXIMITY SWITCHES AND CORDSETS
Type	Tubular photoelectric sensor

Packaging

Carton	1
Weight Per each	0.67

Uses, Certifications, and Standards

Application	Vehicles: On-Road - PickUp & Delivery: Food
Operating Temperature standard	-40° to 158°F (-40° to 70°C) UL Recognized,cUL Recognized