

Eaton 1350E-6514

Catalog Number: 1350E-6514

Eaton Enhanced 50 Series Photoelectric Sensor, Photoelectric, Right Angle, Sensor distance: 5 Ft., 3A max AC, SPDT Form C Relay, 3A at 240 Vac, 6.6 Ft. (2m) Cable, 12–240 Vdc 24–240 Vac input, Diffuse Reflective

General specifications



Product Name	Catalog Number
Eaton Enhanced 50 photoelectric sensor	1350E-6514
UPC	Product Length/Depth
782116111459	1.91 in
Product Height	Product Width
2.1 in	1.81 in
Product Weight	Warranty
0.5375 lb	3 year
Compliances	Certifications
Contact Manufacturer CE Marked	CSA Certified

defaultTaxonomyAttributeLabel

Contact Rating

3A at 240 Vac

Enclosure material

Fiberglass reinforced plastic

Operating mode

Diffuse reflective

Connection

6.6 ft (2 m) cable

Contact configuration

SPDT form C relay

Sensor type

Diffuse reflective

Switch type

Photoelectric

Input voltage

12-240 Vdc, 24-240 Vac

LED indicator

Output status: green

Power on: yellow

Marginal gain: red

Maximum AC current

3 A

Operating temperature - max

131 °F

Operating temperature - min

-13 °F

Environmental rating

IP67, IP69K

Resources

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - 1350E-6514](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)