

Eaton 1372AS3335

Catalog Number: 1372AS3335

Eaton 70 Series Photoelectric Sensor Head, Photoelectric, Right Angle, Sensor distance: Depends on controller used, Aluminum enclosure, Slot Sensor, 35 Ft. (10.7m)

General specifications



Product Name	Catalog Number
Eaton 70 series photoelectric sensor head	1372AS3335
	UPC
	782113970646
Product Length/Depth	Product Height
0.31 in	1.26 in
Product Width	Product Weight
0.31 in	0.3063 lb
Warranty	Compliances
3 year	Contact Manufacturer

Cable type

Polyvinyl Chloride (PVC)

Enclosure material

Aluminum

Operating mode

Slot sensor

Sensor type

Slot sensor

Switch type

Photoelectric

Cord length

420 ft

Operating temperature - max

140 °F

Operating temperature - min

32 °F

Environmental rating

NEMA 1

Specifications and datasheets[Eaton Specification Sheet - 1372AS3335](#)

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)