

# Eaton 14126-4XSCHC

Catalog Number: 14126-4XSCHC

Eaton B-Line series JIC panel enclosure, 14" height, 6" length, 12" width, NEMA 4X, Hinged cover, 4XSCHC enclosure, Wall mount, Small single door, External mounting feet, 304 stainless steel, Seamless poured in-place gasket

## General specifications



Photo is representative

Product Name	Catalog Number
Eaton B-Line series JIC panel enclosure	14126-4XSCHC
UPC	Product Length/Depth
782051702644	6 in
Product Height	Product Width
14 in	12 in
Product Weight	Certifications
12.8 lb	UL 50
	CSA C22.2.
	NEMA

## Material/finish

### Material

304 stainless steel

### Wall thickness

16 gauge

### Finish color

#4 brushed

### Color

Gray

## Model

### Style

Small single door

### Model

4XSCHC enclosure

### Cover type

Hinged

### Mounting method

Wall

### Mounting hole details

External mounting feet

### Closure type

Hinged

### Special features

Cont. piano hinge, panel mount prov., s.s. doorclamps

## Standards

### NEMA Rating

4X

### Country of origin

US

## Resources

### Catalogs

[Electrical Enclosure Catalog](#)

### Specifications and datasheets

[Eaton Specification Sheet - 14126-4XSCHC](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)