HALO

DESCRIPTION


Adjustable slot aperture trim for 12V low voltage 4" H1499 family recessed housings. Die cast trim ring with slot aperture. Trim is available in a variety of finishes. Three "cat's paw" springs secure trim in housing.

| Catalog # | Туре |
|-------------|------|
| Ducient | |
| Project | |
| Comments | Date |
| | |
| Prepared by | |

SPECIFICATION FEATURES

- · Precision die cast metal trim ring with slot aperture
- · For directional accent lighting
- 35° tilt, 360° rotation
- Friction clip "cat paw" retention
- Clear cover glass included with each trim, for use with non-cover glass MR16 lamps

| Housings | | Max Lamp Compatibility |
|-----------|-----------|------------------------|
| H1499TAT | H1499RTAT | - 50W 12V MR16 |
| H1499ICAT | H1499TCP | |
| H1499T75 | | 75W 12V MR16 |



Dimensions* A: 2-1/8" x 1-3/8" [53mm x 35mm] H: 1-1/4" [32mm] OD: 5" [129mm]

ORDERING INFORMATION

| SAMPLE NUMBER: 1420SN | | |
|--|---|--|
| Trim | Finish | |
| 1420= 4" Adjustable Slot Aperture, 35° Tilt | P=Slot Aperture, White Trim SN=Slot Aperture, Satin Nickel Trim TBZ=Slot Aperture, Tuscan Bronze Trim | |

*Key: A: Luminous Aperture, H: Height, OD: Trim Outside Diameter



Specifications and dimensions subject to change without notice.



1420P Slot Aperture, White Trim



1420SN Slot Aperture, Satin Nickel Trim



1420TBZ Slot Aperture, Tuscan Bronze Trim

1420

4-Inch Adjustable Slot Aperture