DESCRIPTION


Reflector trim for 12V low voltage 4" H1499 family recessed housings. Die cast trim ring with metal reflector. Reflector and trim ring available in a variety of finishes. Three "cat's paw" springs secure trim in housing.

Catalog #	Туре
Project	
Comments	Date
Prepared by	

SPECIFICATION FEATURES

- · Precision die cast metal trim ring with spun reflector cone
- · Provides general illumination
- 35° Tilt
- Friction clip "cat paw" retention
- Clear cover glass included with each trim, for use with non-cover glass MR16 lamps

Housings		Max Lamp Compatibility
H1499TAT	H1499RTAT	50W 12V MR16
H1499ICAT	H1499TCP	50VV 12V IVIK16
H1499T75		75W 12V MR16



Dimensions

H: 1-3/8" [33mm] OD: 5" [129mm]

ORDERING INFORMATION

SAMPLE NUMBER: 4001WB

GAIN EL NOMBER. 4001WB		
Trim	Finish	
1421 = 4" Reflector	MB=Black Specular Reflector, White Trim W=White Reflector, White Trim H=Haze Reflector, White Trim C=Clear Specular Reflector, White Trim RG=Residential Gold Reflector, White Trim CG=Champagne Gold Reflector, White Trim SN=Satin Nickel Reflector and Trim TBZ=Tuscan Bronze Reflector and Trim	



1421C Clear Specular Reflector with White Trim Ring



1421CG Champagne Gold Reflector with White Trim Ring



1421RGResidential Gold Reflector with
White Trim Ring



1421H Haze Reflector with White Trim Ring



1421MB Black Specular Reflector with White Trim Ring



1421SN Satin Nickel Reflector with Satin Nickel Trim Ring



Tuscan Bronze Reflector with Tuscan Bronze Trim Ring



1421WWhite Reflector,
White Trim

1421

4-Inch Reflector