# HALO

## DESCRIPTION

Retractable Elbow trim for 12V low voltage 4" H1499 family recessed housings. Elbow tilts 60° and rotates 360°. Die cast elbow and trim ring available in a variety of finishes. Three "cat's paw" springs secure trim in housing.

Catalog #	Туре
Project	
Comments	Date
Prepared by	

## SPECIFICATION FEATURES

- Precision die cast metal trim ring with matching finish retractable elbow.
  For directional accent lighting
- 60° Tilt, 360° rotation
- 60° Filt, 360° rotation
- Friction clip "cat paw" retention
- Clear cover glass included with each trim, for use with non-cover glass MR16 lamps

Housings		Max Lamp Compatibility			
H1499TAT	H1499RTAT	50W 12V MR16			
H1499ICAT	H1499TCP				
H1499T75		75W 12V MR16			



1496P White Elbow



1496SN Satin Nickel Elbow



1496TBZ Tuscan Bronze Elbow


# 1496

Retractable Elbow 4" Trim

	SI
LISTED	
For use in H	lalo listed housings.



Select trims are classified for use in others housings. See www.cooperlighting.com.



Dimensions: A: 1-3/4"[44mm] H: 1-1/8" [29mm] OD: 5" [129mm]

#### **ORDERING INFORMATION**

SAMPLE NUMBER: 1496WH Trim 1496= 4° Retractable Elbow, 60° tilt

WH=White SN=Satin Nickel TBZ=Tuscan Bronze

# HALO HOUSING COMPATIBILITY

Trim #	Style							
		H995ICAT	H995RICAT					
		H457ICAT1E	H457RICAT1E	H457TATE010	H457RTATE010	H457TCPE010	EL4069xx	
		H99ICAT	E4ICATSB					
<b>1496</b> F	Retractable	HISICAI	E4IGAI 3D					
		H99TAT	H99RTAT	E4TATSB	E4RTATSB			
		H1499ICAT	H1499TAT	H1499TCP	H1499RTAT	H1499T75		
		•	•	•	•	•		

For use in select other's housings, refer to U.L. classification list at www.cooperlighting.com.

\*UL1993 listed LED & CFL equivalent lamps permitted. Consult lamp manufacturer for conditions of use. Cooper Lighting Solutions does not warranty the lamp.



Cooper Lighting Solutions 1121 Highway 74 South Peachtree City, GA 30269 P: 770-486-4800 www.cooperlighting.com

Specifications and dimensions subject to change without notice.