

Specifications



Eaton 14W33

Eaton Arrow Hart watertight straight blade plug, #18-10 AWG, 20A, Industrial, 125V, Back wire, Yellow, Nickel-plated brass, IP67, Santoprene thermoplastic elastomer, 5-20P, Two-pole, three-wire, grounding, Screw, 0.30-0.65" in diameter, Thermoplastic, Bulk

General specifications

| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton Arrow Hart watertight straight blade plug |
| CATALOG NUMBER | 14W33 |
| UPC | 040893630977 |
| PRODUCT LENGTH/DEPTH | 1.81 in |
| PRODUCT HEIGHT | 3.44 in |
| PRODUCT WIDTH | 1.81 in |
| PRODUCT WEIGHT | 0.24 lb |
| CERTIFICATIONS | cULus Listed |
| PRODUCT TYPE | Watertight |



Powering Business Worldwide

Electrical Ratings

| | |
|--------------------|---------------------------------|
| AMPERAGE RATING | 20A |
| NEMA CONFIGURATION | 5-20P |
| NUMBER OF POLES | Two-pole |
| NUMBER OF WIRES | 3 |
| RECEPTACLE TYPE | Two-pole, three-wire, grounding |
| TORQUE RATING | 14 lbf-inch |
| VOLTAGE RATING | 125V |

Installation Specifications

| | |
|---------------------|------------|
| ALLOWABLE WIRE SIZE | #18-10 AWG |
| CONNECTION TYPE | Screw |
| WIRING METHOD | Back wire |

Product Specifications

| | |
|--------------------|------------------------------------|
| APPLICATION | Industrial |
| CORD RANGE | 0.30-0.65" in diameter |
| DESIGN TYPE | Straight blade |
| DEVICE GRADE | Watertight special use |
| FACE/BODY MATERIAL | Santoprene thermoplastic elastomer |
| MATERIAL | Thermoplastic |
| STYLE TYPE | Straight body |
| TYPE | Complex environment |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:

Environmental Specifications

| | |
|--------------------------|----------|
| ENVIRONMENTAL CONDITIONS | Damp/wet |
| ENVIRONMENTAL RESISTANCE | IP67 |

Material Specifications

| | |
|------------------|---------------------|
| COLOR | Yellow |
| CONTACT MATERIAL | Nickel plated brass |
| DESIGN TYPE | Straight blade |
| PACKAGING TYPE | Bulk |

Resources

| | |
|-------------------------------|---|
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - 14W33 Arrow Hart watertight locking plugs, connectors and receptacles spec sheet |
|-------------------------------|---|



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications



Eaton 14W33

Eaton Arrow Hart watertight straight blade plug, #18-10 AWG, 20A, Industrial, 125V, Back wire, Yellow, Nickel-plated brass, IP67, Santoprene thermoplastic elastomer, 5-20P, Two-pole, three-wire, grounding, Screw, 0.30-0.65" in diameter, Thermoplastic, Bulk

General specifications

| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton Arrow Hart watertight straight blade plug |
| CATALOG NUMBER | 14W33 |
| UPC | 040893630977 |
| PRODUCT LENGTH/DEPTH | 1.81 in |
| PRODUCT HEIGHT | 3.44 in |
| PRODUCT WIDTH | 1.81 in |
| PRODUCT WEIGHT | 0.24 lb |
| CERTIFICATIONS | cULus Listed |
| PRODUCT TYPE | Watertight |



Powering Business Worldwide

Electrical Ratings

| | |
|--------------------|---------------------------------|
| AMPERAGE RATING | 20A |
| NEMA CONFIGURATION | 5-20P |
| NUMBER OF POLES | Two-pole |
| NUMBER OF WIRES | 3 |
| RECEPTACLE TYPE | Two-pole, three-wire, grounding |
| TORQUE RATING | 14 lbf-inch |
| VOLTAGE RATING | 125V |

Installation Specifications

| | |
|---------------------|------------|
| ALLOWABLE WIRE SIZE | #18-10 AWG |
| CONNECTION TYPE | Screw |
| WIRING METHOD | Back wire |

Product Specifications

| | |
|--------------------|------------------------------------|
| APPLICATION | Industrial |
| CORD RANGE | 0.30-0.65" in diameter |
| DESIGN TYPE | Straight blade |
| DEVICE GRADE | Watertight special use |
| FACE/BODY MATERIAL | Santoprene thermoplastic elastomer |
| MATERIAL | Thermoplastic |
| STYLE TYPE | Straight body |
| TYPE | Complex environment |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:

Environmental Specifications

| | |
|--------------------------|----------|
| ENVIRONMENTAL CONDITIONS | Damp/wet |
| ENVIRONMENTAL RESISTANCE | IP67 |

Material Specifications

| | |
|------------------|---------------------|
| COLOR | Yellow |
| CONTACT MATERIAL | Nickel plated brass |
| DESIGN TYPE | Straight blade |
| PACKAGING TYPE | Bulk |

Resources

| | |
|-------------------------------|---|
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - 14W33 Arrow Hart watertight locking plugs, connectors and receptacles spec sheet |
|-------------------------------|---|



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

