

Specifications



Eaton 14W33

Eaton Arrow Hart watertight straight blade plug, #18-10 AWG, 20A, Industrial, 125V, Back wire, Yellow, Nickel-plated brass, IP67, Santoprene thermoplastic elastomer, 5-20P, Two-pole, three-wire, grounding, Screw, 0.30-0.65" in diameter, Thermoplastic, Bulk

General specifications

PRODUCT NAME	Eaton Arrow Hart watertight straight blade plug
CATALOG NUMBER	14W33
UPC	040893630977
PRODUCT LENGTH/DEPTH	1.81 in
PRODUCT HEIGHT	3.44 in
PRODUCT WIDTH	1.81 in
PRODUCT WEIGHT	0.24 lb
CERTIFICATIONS	cULus Listed
PRODUCT TYPE	Watertight



Powering Business Worldwide

Electrical Ratings

AMPERAGE RATING	20A
NEMA CONFIGURATION	5-20P
NUMBER OF POLES	Two-pole
NUMBER OF WIRES	3
RECEPTACLE TYPE	Two-pole, three-wire, grounding
TORQUE RATING	14 lbf-inch
VOLTAGE RATING	125V

Installation Specifications

ALLOWABLE WIRE SIZE	#18-10 AWG
CONNECTION TYPE	Screw
WIRING METHOD	Back wire

Product Specifications

APPLICATION	Industrial
CORD RANGE	0.30-0.65" in diameter
DESIGN TYPE	Straight blade
DEVICE GRADE	Watertight special use
FACE/BODY MATERIAL	Santoprene thermoplastic elastomer
MATERIAL	Thermoplastic
STYLE TYPE	Straight body
TYPE	Complex environment

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:

Environmental Specifications

ENVIRONMENTAL CONDITIONS	Damp/wet
ENVIRONMENTAL RESISTANCE	IP67

Material Specifications

COLOR	Yellow
CONTACT MATERIAL	Nickel plated brass
DESIGN TYPE	Straight blade
PACKAGING TYPE	Bulk

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - 14W33 Arrow Hart watertight locking plugs, connectors and receptacles spec sheet
-------------------------------	---



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

