



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



14W33 STR Blade IP67 Plug 20A 125V 5-20P

Pass & Seymour/Legrand

Catalog Number	14W33
Manufacturer	Pass & Seymour/Legrand
Description	Rated Watertight For 1, 500 Psi High-Pressure Hosedown, Pass and Seymour Plugs and Connectors Feature Multiple Seals to Ensure Protection Against The Environment. Constructed Of A Sturdy Rubber Body, Which Makes Them Impact- and Chemical-Resistant, They Have Nickel-Plated Blades and Contacts For Superior Corrosion Resistance.
Weight per unit	0.2865 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	20
indoor/outdoor	Both
Material	Rubber
Number of Wires	3
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wire Size	14-12

Dimensions and Weight

Size	4.75"
------	-------

Descriptions

Description	STR BLADE IP67 PLUG 20A 125V 5-20P
extra long description	P&S 14W33 STR BLADE IP67 PLUG 20A 1
Features	Watertight
Long Description	Rated watertight for 1,500 psi high-pressure hosedown, Pass and Seymour plugs and connectors feature multiple seals to ensure protection against the environment. Constructed of a sturdy rubber body, which makes them impact- and chemical-resistant, they have nickel-plated blades and contacts for superior corrosion resistance.
Product Type	STR Blade IP67 Plug 20A 125V 5-20P
Special Features	Quick drive assembly screws, floating blades, rubber body construction, multiple ring seals



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007114300
Manufacturers Part Number	14W33
UPC	785007114300

Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	PLUG

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	10
Weight Per each	0.2865

Uses, Certifications, and Standards

Application	Commercial
nema rating	5-20P
standard	UL, CSA, UL 498