



Job Name:

Job Type:

Comments:

Quantity:

## 15030-07: Quality Max & Energy Star 52 Inch Ceiling Fan in Weathered Iron Finish



### Dimensions:

Diameter:	52"
Blades / Pitch:	5 Blades - 11 ° Pitch
Weight:	18.37 lbs.
Number Of Speeds:	3
Reverse Switch:	Manual
Rev. Switch Location:	Switch Housing
Motor Size:	153.0 X 15.0
Diameter of Housing:	11.0
Capacitor Value:	4.5+6+5/350V/90C
Lead Wire Length:	78 inches
Remote Included:	None
Remote Group(s):	A,B,D,E

### Features:

- ENERGY STAR® Qualified
- Flush mount hardware is included

**Collections:** Quality Max (Primary)  
Manor House

**UPC #:**785652503160

**Finish:** Weathered Iron (07)

**Blade Finish:** Walnut

**Blade Finish 2:** Undefined

### Material List:

1 Body - Steel - Weathered Iron  
5 Blade - MDF with Veneer - Walnut

### Safety Listing:

UL Listed for Dry Locations  
cUL Listed for Dry Locations

### Instruction Sheets:

Bilingual (English - French) (HC-1845FB)

### Blade Details:

Blade Group	Diameter	Included	RPM Hi	CFM Hi	Watts Hi	Amps Hi	RPM Med	CFM Med	Watts Med	Amps Med	RPM Low	CFM Low	Watts Low	Amps Low
	52	Yes	181.0	6181.81	66.0	0.55	120.0	3899.58	29.6	0.39	65.0	1926.8	9.1	0.22

### Mounting Options:

Mounting Type	Included	Item	Downrod Length	Downrod Diameter	Overall Height	Blade to Ceiling	Min. Ceiling Height	Canopy Style	Canopy Diameter
Downrod (Included)	yes		4.0	0.5	12.6	11.93	7.99	Dual Mount	5.16
Flush (Included)	yes				9.25	8.07	7.67	Dual Mount	5.16
Flush (Optional)	no	MC192-07			9.25	8.07	7.67	Heavy Duty Flush Mount Canopy	5.16

### Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Frts. Class	UPS Ship
Individual	15030-07	1	785652503160	21.25	10	10	1.23	16.6	70	Yes
NJ Pallet		56		48	40	77	85.556	929.6		No
NV Pallet		56		48	40	77	85.556	929.6		No