


72547 - 150PS25/RS/STG

GE saf-t-gard® 150/133 watt PS25 1-pack

- 130/120 volts
- GE saf-t-gard® bulbs feature a protective Teflon® coating that helps contain glass fragments if broken. Designed with heavy-duty, all-weather construction, these bulbs protect against shattering, rain breakage and splatter from oil and lubricants. GE saf-t-gard® bulbs are perfect for home use in kitchens, basements garages, workshops and enclosed exterior fixtures
- Lasts 0.9/2.4 years based on 3 hours per day usage
- Estimated yearly energy costs \$18.07/\$16.02 based on 3 hours per day \$0.11 per kWh
- Provides 2160/1650 lumens
- PS25 shape with medium base for use in rough service applications









GENERAL CHARACTERISTICS

Lamp Type Incandescent - A-line

Bulb PS25

Base Medium Screw (E26)

Filament C-17
Bulb Finish Inside frost

Primary Application Rough Service; Shatter-

Resistant

1000.0 hrs

PHOTOMETRIC CHARACTERISTICS

Initial Lumens 2160.0 /1650.0

Nominal Initial Lumens per Watt 14 /12

ELECTRICAL CHARACTERISTICS

Wattage 150.0 Voltage 130.0

DIMENSIONS

Maximum Overall Length 6.9300 in(176.0 mm)

(MOL)

Rated Life

Bulb Diameter (DIA) 2.375 in(60.3 mm) Light Center Length (LCL) 5.180 in(131.6 mm)

PRODUCT INFORMATION

Product Code 72547

Description 150PS25/RS/STG

Standard Package Case

Standard Package GTIN 10043168725474

Standard Package Quantity 60
Sales Unit Unit
No Of Items Per Sales Unit 1
No Of Items Per Standard 60

Package

UPC 043168725477