



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



1547 Straight Blade Rubber Conn 15A 125V 5-15R

Pass & Seymour/Legrand

Catalog Number	1547
Manufacturer	Pass & Seymour/Legrand
Description	Straight Blade Plug, 15 A, 125 V, 2 Poles, 3 Wires, Yellow, -40 °C Operating Temperature, +75 °C Operating Temperature, Screw Terminal, 1.58 In Diameter, 3.10 In Length, #18 to #10 Awg Wire Size, Corrosion Resistant, Impact Resistant, Oil Resistant, Chemical Resistant, Heat Resistant, Weather Resistant, 0.26 LB
Weight per unit	0.2560 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	15
indoor/outdoor	Indoor
Poles	2
Voltage	125.0 V
Voltage Rating	125

Dimensions and Weight

Size	3.25"
------	-------

Descriptions

Description	STRAIGHT BLADE RUBBER CONN 15A 125V 5-15R
extra long description	P&S 1547 STR BLD RUBBER CONN 15A 12

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007114126
UPC	785007114126

Taxonomies, Classifications, and Categories

Category Description	Residential cord connectors
Type	CONNECTOR

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	1
Package	20
Weight Per each	0.256

Uses, Certifications, and Standards

standard	UL, CSA, UL498
----------	----------------