

## **Bridgeport Fittings Inc.**

705 Lordship Blvd. Stratford, CT 06615


Phone: 203-377-5944 Fax: 203-381-3488

# Zinc - Threaded

# **Images**



Download Photo Image



**Download Dimensional Image** 

Dimension A in Inches: 1-1/4 Dimension B in Inches: 7/8 Dimension C in Inches: 2-3/4

#### **Application**

To secure threaded rigid service entrance conduit to box or enclosure. Insulated throat rated 105 degree c. UL listed Type 4 - Watertight. Suitable for Aluminum and Steel Rigid Conduit.

#### **Product Information**

Material: Zinc Die Cast

Finish: Ball burnished, mirror smooth

### **Certifications & Codes:**

CSA File Number: LR39354
Federal Specification Number: A-A-50553
NEMA Standard: FB-1
UL File Number: E9391
UL Standard: UL-514B
UNSPSC: 39121311

Catalog ID: 156-DC

**UPC Number:** 781747091567

Description: Threaded Hub, Zinc Die Cast, Size 2 Inch

**Application:** To secure threaded rigid service entrance conduit to box or enclosure. Insulated throat rated 105 degree c. UL listed Type 4 - Watertight. Suitable for

Aluminum and Steel Rigid Conduit.

Trade Size: 2"

Country of Manufacture: USA

Std Pkg Qty: 20

Unit Qty: 2