

## 15 Amp In-Line Portable GFCI, Manual Reset

1594PC2M



Portable Ground Fault Circuit Interrupter, 2'  
Cord 15amp 125volt, Manual Reset

### features & benefits

- Durable polycarbonate case withstands hard use.
- In-line has bright, green power indicator light that is on when power is available and is visible from both sides of the GFCI.
- Open neutral protection.
- Optional Turnlok plugs and connectors prevent accidental disconnection.
- Optional tri-cord connector handles up to three loads.

### specifications

**General Info**

Type: In-Line Portable GCI, Manual Reset

**Listing Agencies/Third Party Information**

cULus: Yes

Federal Spec: No

UL Listing No: UL943, UL498

UL Standard: Yes

UN SPS C: 39121614

**Dimensions**

Length U S: 27.75"

**Technical Information**

Amps: 15 Amp

Volts: 125

Volts A C: 125

**Buy American Act Compliance**

Country of Origin: CHINA

Buy American Act Status: No