



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



15971 Radiant Self Test Duplex GfcI 15A 125V Iv

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | 15971 |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Duplex Receptacle, 15 A, 125 V, 2 Poles, #14 to #10 Awg Compatible Wire Size, Control Circuit Actuator, Back and Side Wired Connection, 60 HZ, 1.73 In Width, 4.20 In Height, Thermoplastic Material, Ivory, 0.025 Sec Trip Time, 0.2800 LB |
| Weight per unit | 0.2750 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|---------------------|---------------------|
| actuator | Control Circuit |
| amperage rating | 15 |
| connection | Back and side wire |
| indoor/outdoor | Indoor |
| interrupt rating | 4 to 6 mA |
| Mounting Type | Box |
| Number of Gangs | 1.0 |
| Number of Wires | 3 |
| Outlet Type | GFCI |
| Poles | 2 |
| trip range | 4 to 6 mA |
| Trip Type | .025 Second Nominal |
| Voltage | 125.0 V |
| Voltage Rating | 125 |
| Wall Plate Included | YES |

Material, Color, and Finish

| | |
|--------|-------|
| Finish | Matte |
|--------|-------|

Dimensions and Weight

| | |
|--------|------|
| Length | 1.03 |
| Width | 1.73 |

Descriptions

| | |
|------------------------|---|
| Description | RADIANT SELF TEST DUPLEX GFCI 15A 125V IV |
| extra long description | P&S 15971 RADIANT SLF TST DUP GFCI |

Manufacturer Information

| | |
|-------|----------------|
| Brand | Pass & Seymour |
| GTIN | 00785007035735 |
| UPC | 785007035735 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------------|
| Category Description | Residential GFCI devices |
| Type | Outlet |

Trade Size

| | |
|----------|------|
| Amperage | 15.0 |
|----------|------|

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.275 |

Uses, Certifications, and Standards

| | |
|--------------------------|-----------------------------------|
| environmental conditions | 95% Humidity, UL 94 V2 |
| Operating Temperature | -35°C to +66°C |
| standard | CULUS, UL, cULus, UL Listed, FSUL |