



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



1597TRLA Radiant Self Test TR Gfci 15A 125V La

Pass & Seymour/Legrand

Catalog Number	1597TRLA
Manufacturer	Pass & Seymour/Legrand
Description	Self-Test Duplex Receptacle, 15 A, 125 V, 2 Poles, #14 to #10 Awg Compatible Wire Size, Control Circuit Actuator, Back and Side Wired Connection, 60 HZ, 1.73 In Width, 4.20 In Height, Thermoplastic Material, Light Almond, 0.025 Sec Trip Time, Tamper Resistant, 0.2800 LB
Weight per unit	0.2750 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

actuator	Control Circuit
amperage rating	15
connection	Back and side wire
indoor/outdoor	Indoor
interrupt rating	4 to 6 mA
Mounting Type	Box
Number of Gangs	1.0
Number of Wires	3
Outlet Type	GFCI, Tamper-Resistant
Poles	2
trip range	4 to 6 mA
Trip Type	.025 Second Nominal
Voltage	125.0 V
Voltage Rating	125
Wall Plate Included	YES

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Length	1.03
Width	1.73

Descriptions

Description	RADIANT SELF TEST TR GFCI 15A 125V LA
extra long description	P&S 1597TRLA RADIANT SELF TEST TR G

Manufacturer Information

Brand	Pass & Seymour
GTIN	00785007035797
UPC	785007035797



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Residential GFCI devices
Type	Outlet

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	1
Package	10
Weight Per each	0.275

Uses, Certifications, and Standards

environmental conditions	95% Humidity, UL 94 V2
Operating Temperature	-35°C to +66°C
standard	UL, CULUS, cULus, UL Listed, FSUL