



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



1597TRW 15A 125V Gfci RCPT

Pass & Seymour/Legrand

Catalog Number	1597TRW
Manufacturer	Pass & Seymour/Legrand
Description	Self-Test Duplex Receptacle, 15 A, 125 V, 2 Poles, #14 to #10 Awg Compatible Wire Size, Control Circuit Actuator, Back and Side Wired Connection, 60 HZ, 1.73 In Width, 4.20 In Height, Thermoplastic Material, White, 0.025 Sec Trip Time, Tamper Resistant, 0.2800 LB
Weight per unit	0.2750 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

actuator	Control Circuit
amperage rating	15 A
connection	Back and side wire
interrupt rating	4 to 6 mA
Poles	2 in
trip range	4 to 6 mA
Trip Type	.025 Second Nominal

Dimensions and Weight

Length	PN14-6FN-C
Width	78119796233

Descriptions

Description	15A 125V GFCI RCPT
-------------	--------------------

Manufacturer Information

Brand	PASS & SEYMOUR
GTIN	00785007035759
sub brand	Pass & Seymour
UPC	785007035759

Taxonomies, Classifications, and Categories

Category Description	Residential GFCI devices
Type	Specification Grade Tamper-Resistant 15A Self-Test Duplex GFCI

Packaging

Carton	1
Weight Per each	0.275

Uses, Certifications, and Standards

environmental conditions	95% Humidity, UL 94 V2
Operating Temperature	-35°C to +66°C
standard	cULus, UL Listed, FSUL