



15W33 Straight Blade IP67 Conn 20A 125V 5-20R

Pass & Seymour/Legrand

Catalog Number	15W33
Manufacturer	Pass & Seymour/Legrand
Description	Rated Watertight For 1, 500 Psi High-Pressure Hosedown, Pass and Seymour Plugs and Connectors Feature Multiple Seals to Ensure Protection Against The Environment. Constructed Of A Sturdy Rubber Body, Which Makes Them Impact- and Chemical-Resistant, They Have Nickel-Plated Blades and Contacts For Superior Corrosion Resistance.
Weight per unit	0.4375 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

indoor/outdoor	Both
Voltage	125.0 V

Descriptions

Description	STRAIGHT BLADE IP67 CONN 20A 125V 5-20R
extra long description	P&S 15W33 STR BLADE IP67 CONN 20A 1
Features	Watertight
Long Description	Rated watertight for 1,500 psi high-pressure hosedown, Pass and Seymour plugs and connectors feature multiple seals to ensure protection against the environment. Constructed of a sturdy rubber body, which makes them impact- and chemical-resistant, they have nickel-plated blades and contacts for superior corrosion resistance.
Product Type	STR Blade IP67 Conn 20A 125V 5-20R

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007114324
Manufacturers Part Number	15W-33
UPC	785007114324

Taxonomies, Classifications, and Categories

Category Description	Industrial cord connectors
----------------------	----------------------------

Packaging

Carton	1
Package	10
Weight Per each	0.4375