

Bridgeport Fittings Inc.

705 Lordship Blvd. Stratford, CT 06615


Phone: 203-377-5944 Fax: 203-381-3488

Zinc - Threaded

Images



Download Photo Image



Download Dimensional Image

Dimension A in Inches: 1-11/16 Dimension B in Inches: 15/16 Dimension C in Inches: 4-3/4

Application

To secure threaded rigid service entrance conduit to box or enclosure. Insulated throat rated 105 degree c. UL listed Type 4 - Watertightnants from entering enclosure. Suitable for Aluminum and Steel Rigid Conduit.

Product Information

Material: Zinc Die Cast

Finish: Ball burnished, mirror smooth

Certifications & Codes:

CSA File Number: LR39354
Federal Specification Number: A-A-50553
NEMA Standard: FB-1
UL File Number: E9391
UL Standard: UL-514B
UNSPSC: 39121311

Catalog ID: 160-DC

UPC Number: 781747091604

Description: Threaded Hub, Zinc Die Cast, Size 4 Inch

Application: To secure threaded rigid service entrance conduit to box or enclosure. Insulated throat rated 105 degree c. UL listed Type 4 - Watertightnants from entering enclosure. Suitable for Aluminum and Steel Rigid Conduit.

Trade Size: 4"

Country of Manufacture: USA

Std Pkg Qty: 5 Unit Qty: Bulk